




Controller



Fixed Angle Rotor



| | | | | |
|--|--|---|---|--|
| <p>1000 ml</p>  <p>V10004A 1000ml x 4tubes 7000 RPM, 9039 G R166mm</p>  | <p>500 ml</p>  <p>V5006A 500ml x 6tubes 9000 RPM, 14570 G R162mm</p> <p>V5004A 500ml x 4tubes 11000 RPM, 21374G R158mm</p>  | <p>250 ml</p>  <p>V2506A 250ml x 6tubes 12000 RPM, 22378 G R139mm</p> <p>V2504A 250ml x 4tubes 13000 RPM, 23807G R126mm</p>  | <p>50 ml - 30 ml</p>  <p>V508A 50ml x 8tubes 22000 RPM, 55193G R102mm</p> <p>V308A 30ml x 8tubes 23000 RPM, 53228G R96mm</p>  | <p>50 ml - conical</p>  <p>V506AC Conical Tube 50ml x 6tubes 15000 RPM, 25155G R100mm</p>  |
| <p>10 ml</p>  <p>V1012A 10ml x 12tubes 24000 RPM, 50873 G R 79mm</p> <p>V1024A 10ml x 24tubes 22000 RPM, 50323G R 93mm</p>  | <p>100 ml</p>  <p>V1006A 100ml x 6tubes 20000 RPM, 43826 G R 98mm</p>  | <p>15 ml</p>  <p>V1512A 15ml x 12tubes 21000 RPM, 54717 G R 111mm</p> <p>V1524A 15ml x 24tubes 18000 RPM, 48028G R119mm</p>  | <p>15 ml - conical</p>  <p>V1512AC conical tube 15ml x 12tubes 15000 RPM, 24503G R99mm</p>  | <p>1.5 ml</p>  <p>V1.524A 1.5ml x 24tubes 24000 RPM, 51517G R 80mm</p>  |

Specification

| Model | VS-24SMTI |
|-------------------|--|
| Speed | 24,000rpm |
| Max Rcf | 55,193xg |
| Timer | 0-99hr |
| Temperature range | -20 to 40°C |
| Pre-condition | Pre-cooling |
| Step mode | 5 step programmable |
| Display | Dual display, LCD |
| Rotor | 1.5ml x 24, 10ml x 12, 10ml x 24, 15ml x 12, 15ml x 24 100ml x 6, 30ml x 6, 50ml x 8, 250ml x 6, 500ml x 4 1000ml x 4, |
| Power | 220VAC |
| Weight | 230kg |